



Guldmann™

Stepless.
by Guldmann

Accessibility Specialists in New England

December 20, 2012
Belmont, MA

Dear Specialist,

At Guldmann Inc. we are very much aware of the challenges related to accessibility for all the citizens of New England with special needs. We also know the challenges you have every day to make sure that all public places have approved and safe access.

As a company that started 30 years ago in a market with strict ADA-like laws (the Scandinavian market) and very specific rules about what you can do to old buildings, Guldmann has developed a range of products that makes your job easier as well as access easier.

Please find enclosed the latest newsletter about Stepless products by Guldmann. You can find more information on www.guldmann.net or call our local New England office in Belmont, MA at 1-800-664-8834 ext. 403

Sincerely,

The Stepless Team by Guldmann




Guldmann, Inc. - Tampa
14401 McCormick Drive, Ste A
Tampa, FL 33626
800-664-8834

Guldmann, Inc.-Northern Office
130 Trapelo Rd, 2nd Flr
Belmont, MA 02478
800-664-8834 Ext 402

Guldmann Inc.-West Coast
5560 Skylane Blvd, Ste C
Santa Rosa, CA 95403
800-664-8834 Ext 301

| Time to care |



Date: 19-12-2012

LP8 – an upgrade makes a lifting capacity of 350 kg possible

Our lifting platform LP8 has got a facelift and an upgrade which entails a lifting capacity of 350 kg and a much nicer appearance with side panels/gates of glass as standard. Below you can read more about the improvements.

With the upgrade the new LP8 features are:


350 kg lifting capacity

The lifting capacity has been upgraded from 300 kg to 350 kg.


Glass panels as standard for a lighter design – makes it easier to integrate the lifting platform into the existing environment. It is still possible to buy the perforated steel plates (option).

Inside wiring – leads to a much nicer appearance

The small cable box on top of the left post has been removed and the loose cable on the left side has been concealed. Now the cable is inside the post – hidden so it does not disturb the appearance of the lifting platform.



New model with inside cables



Old model with outside cables

Overload protection

If the lifting platform is overloaded, an indicator lamp will turn on and a sound will start - and the platform will not lift or lower. After the overload has been removed, the platform can operate again.



Lock on the upper gate is concealed

The door mechanism on the upper gate is no longer visible. Moreover, when it is concealed it is more protected.

Gas spring on the upper gate so it can be opened mechanically

On the old model people sometimes damaged the door because they tried to open it manually – now it is possible to open the automatic gate manually without breaking the door.

Applicable in temperatures from -40° to +50°C

The new electronics mean among other things that the LP8 may be used in temperatures from -40° to +50° C.

Council Directive 2006/42/EEC & EN81-41

LP8 is manufactured according to the new machine directive & to relevant requirements in EN-81-41. The lifting platform has been approved by a notified body (DNV 0434).

Installation

In terms of installation there are no major changes – it is still easy to install the LP8. We recommend that you use our lifting beam when craning the lifting platform as it makes the lifting and moving of the platform much easier and safe.

Using a crane:


When using a crane a lever / lifting beam is necessary - please see the illustration pos. 2. The lever / lifting beam (item number 30903239) is delivered complete with lifting beam, straps etc. and can be reused.

Pos. 1 Fixing of lifting beam.

Pos. 2 Lifting beam.

Pos. 3 Connection strap. To be used for fixing the lifting beam in the front of the lift frame (is incl. in item no. 30903239).

Pos. 4 Fixing point of lifting beam.



Using a forklift:

The lifting platforms are put on pallets and can be moved with a forklift.

Release date

The new LP8 will be released by the end of November 2012. All new orders will as of today be the new LP8.